

BU-5070-B-XX-0**(Test Lead: Dual Stackable Banana Plug to Male BNC)**

- The BU-5070-B-0 is a test lead with a dual stackable, 4mm banana plug to a male BNC connector. The banana plug mates with any standard 4mm banana jacks with industry standard 0.75" (19mm) center-to-center spacing.
- Constructed with RG58/U coaxial cable. Center conductor is 20 AWG (19x33) tinned copper and the shield is tinned copper braid (95% coverage).
- Material: Overmold Polypropylene
 BNC Nickel-plated brass
- Rating: Current 50 Ohms
 Voltage Hands-free testing to 500 VRMS
- Length: The "XX" in the model number represents the overall length in inches. Standard lengths are: 12" (30cm), 24" (61cm), 36" (.9m), 48" (1.2m)
- RoHS 3 compliant, exemption 6c

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mueller Electric:](#)

[BU-5070-B-24-0](#) [BU-5070-B-60-0](#) [BU-5070-B-48-0](#) [BU-5070-B-12-0](#)