

BU-P2269

(Double Banana Jack, Panel Mount)



- The BU-P2269 is a mountable double banana jack. Can be mounted to panels up to 0.25" thick. Wire can be soldered to pin ends.
- Material: Body Nylon
 Contacts Nickel-plated brass
- Overall length 1.22" (30.99mm), overall width 1.38" (35.05mm)
- Mounting:
 - Mount thru panels up to 0.25" (6.35mm) thick. Recommended panel cutout is 2X Ø0.375" (9.52mm) holes spaces 0.75" (19.05mm) apart center-to-center.
- Ratings:
 - Amperage: 15 Amps
 - Voltage: Hand-held 30 VAC/60VDC
 Hands-free 2500 Vrms max in controlled environments
 - Temperature: -50°C to 120°C
- RoHS compliant

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mueller Electric:](#)

[BU-P2269](#)