

BU-P3750-@
(Gold-plated Binding Post, Panel Mount)



- The BU-P3750 is a panel mount, gold-plated binding post that accepts unshrouded or retractable 4mm banana plugs, bare wire, or spade plugs.
- Overall length 1.78" (45.2mm), OD = 0.44" (11.2mm)
- Mounts through panels between 0.070" and 0.25" thick with a $\varnothing 0.375$ " (9.52mm) hole.
- Material: Contacts Gold-plated brass
 Insulator Polycarbonate
- Rating: Current 15 Amps
 Voltage Hands-free testing to 2500 VRMS
 Temperature -50°C (-58°F) to 115°C (239°F)
- Color: The "@" in the model number indicates color.
 Available colors: -0 Black, -2 Red
- RoHS 3 compliant, exemption 6c

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mueller Electric:](#)

[BU-P3750-2](#) [BU-P3750-0](#)