

BU-P4543-@**(Dual Pin Tip Jack)**

- The BU-P4543 is a dual pin tip jack. Can be mounted to panels up to 0.25" thick.
- Overall length 0.88" (22.35mm), overall width 0.86" (21.84mm)
- Material: Body Nylon
 Contacts Gold-plated beryllium copper
- Mounting: Mount thru panels up to 0.25" (6.35mm) thick. Recommended panel cutout is 2X Ø0.25" (6.35mm) holes spaces 0.50" (12.7mm) apart center-to-center.
- Ratings: Current 5 Amps
 Voltage Hands-free testing to 1500 VRMS
 Temperature -50°C to 120°C
- Color: The "@" in the part number is the color of the nylon center spacer.
 Available colors: -0 Black, -2 Red
- RoHS 3 compliant, exemption 6c

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mueller Electric:](#)

[BU-P4543-2](#) [BU-P4543-0](#)