

### BU-P5219 (Triaxial Female Bulkhead Receptacle)



- The BU-P5219 is a female 3 lug connector with a Max Panel Thickness of 0.14" (3.56mm)
- Panel cut out is 0.417" (10.59mm) high and 0.453" (16.5mm) wide.
- Mates with the 3 lug male version (5218)
- Material:
  - Body – Nickel plated Brass, Tarnish Resistant
  - Center Contact – Gold plated Beryllium Copper
  - Outer Contact – Gold plated Beryllium Copper
  - Dielectric - PTFE
- Color: The "@" in the model number indicates color.  
Available colors are: -0 Black, -2 Red
- RoHS 2 Compliant

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mueller Electric:](#)

[BU-P5219](#)