

WI-M-10-XX-@

(Heavy-duty 10 AWG, Silicone Jacket Test Lead Wire)



- Mueller's WI-M-10 is "Coolflex 45" wire that is 10 AWG, 1064 strand 56/08x19C, tinned copper wire with highly flexible 0.197" (5mm) diameter silicone jacket.
- Ratings: Current 45 Amps @ 150°C
 Voltage 600V
- Length: The "XX" in the model number indicates length in feet.
 Standard lengths: 10', 25', *50', *100'
 (custom lengths available upon request)
 * = **Sold as spooled wire**
- Color: The "@" in the model number represents color. Available colors:
 -0 Black, -2 Red, -4 Yellow, -5 Green, -6 Blue, -9 White
- RoHS 3 compliant

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mueller Electric:

[WI-M-10-10-0](#) [WI-M-10-25-6](#) [WI-M-10-10-4](#) [WI-M-10-25-2](#) [WI-M-10-10-6](#) [WI-M-10-10-5](#) [WI-M-10-25-9](#) [WI-M-10-25-0](#) [WI-M-10-25-4](#) [WI-M-10-25-5](#) [WI-M-10-10-9](#) [WI-M-10-10-2](#)