

WI-M-20-XX-*

(Superior 22 AWG, Silicone Jacket Test Lead Wire)



- 20 AWG, xxx/xx strand (x/xx/.xxmm) copper with a highly flexible, .xxx" (xx.xmm) diameter silicone jacket.
- Ratings: 1000V, 14 Amps. Max Operating Temperature: 150°C (302°F)
- Length: "XX" in model number indicates length in feet. Standard lengths are: -10 Ft. and -25 Ft. Custom lengths are available upon request
- Colors: designated by "*" in the part number: -0 black, -2 red,
- RoHS Compliant

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mueller Electric:](#)

[WI-M-20-0](#) [WI-M-20-2](#)