

BU-24 Series

(Grounding Clip)



BU-24APN



BU-24APS



BU-24APN-DZZZ



BU-24APN-HOOK

- The BU-24 series of clips are grounding clips. Compatible with Mueller BU-26 PVC insulators.
- Overall length 2.84" (72.2mm), maximum jaw spread = 0.75" (19mm), BU-24APN-HOOK length = 4" (101.6mm), hook diameter = 0.55" (14mm)
- Connects to wire up to 10 AWG via crimp or screw connection (included).
- Material: Clip Zinc-plated steel
 Spring Steel
- Ratings: Current 25 Amps
- The BU-24 is sold under the following models:

BU-24APN	Zinc-plated steel clip
BU-24APS	Zinc-plated steel clip, stamped "+"
BU-24APN-DZZZ	BU-24APN clip with screw separate
BU-24APN-HOOK	BU-24APN-HOOK with attached hook
- RoHS 3 compliant

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mueller Electric:](#)

[BU-24APS](#) [BU-24APN](#) [BU-24APN-HOOK](#)