

## BU-60-@ Series

(Insulated and Handled Steel Alligator Clips)



BU-60H-@



BU-60HPR-@



BU-60HS-@



BU-60TBO-@ / BU-60X-@

- Mueller Electric's BU-60 is the most common and versatile alligator clip.
- Overall length 2.3" (58mm), overall width 0.38" (10mm), maximum jaw spread = 0.31" (7.9mm)
- Ratings:                      Current              10 Amps
- The BU-60 is sold under the following handled and insulated models:
 

BU-60H-@	Nickel-plated steel clip with colored acetate handle, compatible with 4mm banana plug connections
BU-60HS-@	BU-60H-@ with a screw for added wire attachment
BU-60HPR-@	BU-60H-@ with probe tip jack, compatible with 0.080" (2mm) probe tip connections
BU-60TBO-@	Insulated BU-60H-@ with 8-32 threaded barrel
BU-60X-@	Insulated stainless-steel BU-60H-@ (including hardware)
- Colors: The "@" in the above part numbers represents the color of the handle or the insulator. Available colors:
 

BU-60H-@ / BU-60HS-@:	-0 Black, -2 Red, -4 Yellow, -5 Green, -6 Blue, -9 White
BU-60HPR-@:	-0 Black, -2 Red
BU-60TBO-@ / BU-60X-@:	-0 Black, -2 Red
- RoHS 3 compliant

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Mueller Electric:

[BU-60HPR-5](#) [BU-60HPR-2](#) [BU-60HPR-0](#) [BU-60HPR-9](#) [BU-60HPR-4](#) [BU-60HPR-6](#) [BU-60H-9](#) [BU-60H-5](#) [BU-60H-4](#) [BU-60H-6](#) [BU-60H-0](#) [BU-60H-2](#) [BU-60HS-5](#) [BU-60HS-9](#) [BU-60HS-6](#) [BU-60HS-4](#) [BU-60HS-0](#) [BU-60HS-2](#)