

**BU-P2142-@**  
(Mini (3mm) Banana Jack)



- The BU-P2142 is a mini banana jack that accepts mini 3mm banana plugs.
- Material:   Housing     Nylon  
                  Contacts    Nickel-plated brass with beryllium copper contact
- Overall length 0.88" (22.35mm)
  - Pole Threads: 8-32
- Mounting:
  - Mount thru panels up to 0.25" (6.35mm) thick. Recommended panel cutout is Ø0.25" (6.35mm) hole.
- Ratings:
  - Current: 5 Amps
  - Voltage: Hands-free testing to 1000 VDC
  - Temperature: -50°C to 105°C
- Color: The "@" in the model number indicates color.  
          Available colors are: -0 Black, -2 Red
- RoHS Compliant

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mueller Electric:](#)

[BU-P2142-0](#) [BU-P2142-2](#)