

BU-P72930-@ (Panel Mount Jack for Sheathed Plugs)



- The BU-P72930 is a panel mount 4mm banana jack with a 4mm stud connection. The jack accepts shrouded, unshrouded, and retractable 4mm banana plugs.
- Overall length of 1.335" (33.9mm) and 0.47" (11.94mm) diameter for panel drilling.
- Material:
 - Body – Polyamide
 - Hex Nut – Nickel plated Brass
 - Stud – Nickel plated Brass
 - Stud Hex Nut – Nickel plated Brass
- Rating:
 - Max Current – 36 Amps
 - Max Voltage – 1,000 V CAT III
- Color: The "@" in the model number indicates color.
Available colors are: -0 Black, -1 Brown, -2 Red, -4 Yellow, -5 Green, -6 Blue, -9 White.
- RoHS 3 Compliant, **CE** Certified

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mueller Electric:](#)

[BU-P72930-1](#) [BU-P72930-5](#) [BU-P72930-9](#) [BU-P72930-2](#) [BU-P72930-4](#) [BU-P72930-0](#) [BU-P72930-6](#)