

BU-PBXX-@

(Test Lead: Stackable Banana Plugs Each End)



- Mueller's BU-PB is a test lead with stackable, 4mm banana plugs on each end. The banana plugs mate with any standard 4mm banana jack.
- Constructed with PVC-jacketed, 18 AWG test lead wire and has color matching overmolded banana plugs.
- Materials:

Banana plug	Nickel-plated beryllium copper
Wire insulation	PVC
Overmold	Polypropylene
- Ratings:

Current	15 Amps
Voltage	Hands-free testing to 1000V
- Length: The "XX" in the part number represents overall length in inches.
Standard lengths: 4", 12", 18", 24", 36", 48", 60", 72"
- Color: The "@" in the model number represents color. Available colors:
-0 Black, -2 Red, -4 Yellow, -5 Green, -6 Blue, -9 White
- RoHS 3 compliant

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mueller Electric:

[BU-PB48-5](#) [BU-PB36-5](#) [BU-PB24-5](#) [BU-PB12-5](#) [BU-PB18-5](#) [BU-PB36-2](#) [BU-PB18-2](#) [BU-PB12-2](#) [BU-PB24-2](#) [BU-PB24-02](#) [BU-PB48-2](#) [BU-PB72-2](#) [BU-PB60-2](#) [BU-PB36-6](#) [BU-PB18-6](#) [BU-PB12-6](#) [BU-PB48-6](#) [BU-PB24-6](#) [BU-PB18-4](#) [BU-PB48-4](#) [BU-PB24-4](#) [BU-PB36-4](#) [BU-PB12-4](#) [BU-PB24-9](#) [BU-PB18-9](#) [BU-PB36-9](#) [BU-PB12-9](#) [BU-PB48-9](#) [BU-PB48-0](#) [BU-PB12-0](#) [BU-PB60-0](#) [BU-PB36-0](#) [BU-PB72-0](#) [BU-PB24-0](#) [BU-PB18-0](#) [BU-PB36-02](#) [BU-PB4-2](#) [BU-PB4-6](#) [BU-PB4-0](#)