

## **BU-PMDP-@**

**(Solderless, Stackable Double Banana Plug with Cable Guide)**



- The BU-PMDP is a double 4mm banana plug with industry standard 0.75" center-to-center plug spacing. Wires can be attached by the axial setscrews and there is a small compartment between the banana plugs which can hold small components.
- Overall length 1.58" (40.13mm), banana jack spacing = 0.75" (19.05mm)
- Material:     Banana plug             Nickel-plated beryllium copper  
                  Body                     Polypropylene
- Rating:
  - Current: 15 Amps
  - Voltage: Hands-free testing to 1500V CAT I
- Color: The "@" in the model number indicates color.  
          Available colors are: -0 Black,   -2 Red,    -5 Green,   -9 White
- RoHS 3 Compliant

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mueller Electric:](#)

[BU-PMDP-2](#) [BU-PMDP-0](#) [BU-PMDP-9](#) [BU-PMDP-5](#)