

## **WI-M-10-XX-@**

**(Extra Heavy-Duty 10 AWG, UL Recognized, Silicone Jacket Test Lead Wire)**



- Mueller's WI-M-10-@ is 10 AWG, 1050/0.08 stranded, tinned copper wire with highly flexible 6mm diameter silicone jacket.
- Ratings:

Voltage	1100V
Dielectric Strength	3.2 KV/Min
Spark Test	10 KV
Rated Temperature	-40°C to 180°C
Temperature Rating	FT2
UL Recognized	UL 3640
- Length: The "XX" in the model number indicated length in feet.  
Standard lengths: 10', 25', 30', 50', and 100'
- Color: The "@" in the model number represents color.  
Available colors: -0 Black, -2 Red

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Mueller Electric:

[WI-M-10-10-0](#) [WI-M-10-25-6](#) [WI-M-10-10-4](#) [WI-M-10-25-2](#) [WI-M-10-10-6](#) [WI-M-10-10-5](#) [WI-M-10-25-9](#) [WI-M-10-25-0](#) [WI-M-10-25-4](#) [WI-M-10-25-5](#) [WI-M-10-10-9](#) [WI-M-10-10-2](#)