

WI-M-8-XX-@

(Extra Heavy-Duty 8 AWG, UL Recognized, Silicone Jacket Test Lead Wire)



- Mueller's WI-M-8-@ is 8 AWG, 1650/0.08 stranded, tinned copper wire with highly flexible 0.256" (6.5mm) diameter silicone jacket.
- Ratings:

Voltage	1100V
Current	90A @ 75°C
	120A @ 104°C
	180A @ 150°C
Dielectric Strength	3.2 KV/Min
Spark Test	10 KV
Rated Temperature	-40°C to 200°C
Flammability Rating	FT2
UL Recognition	3640
- Length: The "XX" in the model number indicated length in feet.
Standard lengths: 10', 25', 30', 50', and 100'
- Color: The "@" in the model number represents color.
Available colors: -0 Black, -2 Red

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mueller Electric:](#)

[WI-M-8-10-2](#) [WI-M-8-25-2](#) [WI-M-8-25-0](#) [WI-M-8-10-0](#)