

**MANUFACTURER'S PART NUMBER**

GRM02-KIT-TTOL-DE

**KIT DESCRIPTION**

01005 Class 1 Tight Tolerance

**KIT CONTENTS****QTY IN KIT****SPECIFICATIONS**

GRM0225C1HR20WA03L  
GRM0225C1HR30WA03L  
GRM0225C1HR40WA03L  
GRM0225C1HR50WA03L  
GRM0225C1HR60WA03L  
GRM0225C1HR70WA03L  
GRM0225C1HR80WA03L  
GRM0225C1HR90WA03L  
GRM0225C1H1R0WA03L  
GRM0225C1H1R1BA03L  
GRM0225C1H1R2BA03L  
GRM0225C1H1R3BA03L  
GRM0225C1H1R4BA03L  
GRM0225C1H1R5BA03L  
GRM0225C1H1R6BA03L  
GRM0225C1H1R7BA03L  
GRM0225C1H1R8BA03L  
GRM0225C1H1R9BA03L  
GRM0225C1H2R0BA03L  
GRM0225C1H2R1BA03L  
GRM0225C1H2R2BA03L  
GRM0225C1H2R3BA03L  
GRM0225C1H2R4BA03L  
GRM0225C1H2R5BA03L  
GRM0225C1H2R6BA03L  
GRM0225C1H2R7BA03L  
GRM0225C1H2R8BA03L  
GRM0225C1H2R9BA03L  
GRM0225C1H3R0BA03L  
GRM0225C1H3R1BA03L  
GRM0225C1H3R2BA03L  
GRM0225C1H3R3BA03L  
GRM0225C1H3R4BA03L  
GRM0225C1H3R5BA03L  
GRM0225C1H3R6BA03L  
GRM0225C1H3R7BA03L  
GRM0225C1H3R8BA03L  
GRM0225C1H3R9BA03L  
GRM0225C1H4R0BA03L  
GRM0225C1H4R1BA03L  
GRM0225C1H4R2BA03L  
GRM0225C1H4R3BA03L  
GRM0225C1H4R4BA03L  
GRM0225C1H4R5BA03L

01005(0402M) COG 0.20pF  $\pm 0.05$ pF 50V  
01005(0402M) COG 0.30pF  $\pm 0.05$ pF 50V  
01005(0402M) COG 0.40pF  $\pm 0.05$ pF 50V  
01005(0402M) COG 0.50pF  $\pm 0.05$ pF 50V  
01005(0402M) COG 0.60pF  $\pm 0.05$ pF 50V  
01005(0402M) COG 0.70pF  $\pm 0.05$ pF 50V  
01005(0402M) COG 0.80pF  $\pm 0.05$ pF 50V  
01005(0402M) COG 0.90pF  $\pm 0.05$ pF 50V  
01005(0402M) COG 1.0pF  $\pm 0.05$ pF 50V  
01005(0402M) COG 1.1pF  $\pm 0.1$ pF 50V  
01005(0402M) COG 1.2pF  $\pm 0.1$ pF 50V  
01005(0402M) COG 1.3pF  $\pm 0.1$ pF 50V  
01005(0402M) COG 1.4pF  $\pm 0.1$ pF 50V  
01005(0402M) COG 1.5pF  $\pm 0.1$ pF 50V  
01005(0402M) COG 1.6pF  $\pm 0.1$ pF 50V  
01005(0402M) COG 1.7pF  $\pm 0.1$ pF 50V  
01005(0402M) COG 1.8pF  $\pm 0.1$ pF 50V  
01005(0402M) COG 1.9pF  $\pm 0.1$ pF 50V  
01005(0402M) COG 2.0pF  $\pm 0.1$ pF 50V  
01005(0402M) COG 2.1pF  $\pm 0.1$ pF 50V  
01005(0402M) COG 2.2pF  $\pm 0.1$ pF 50V  
01005(0402M) COG 2.3pF  $\pm 0.1$ pF 50V  
01005(0402M) COG 2.4pF  $\pm 0.1$ pF 50V  
01005(0402M) COG 2.5pF  $\pm 0.1$ pF 50V  
01005(0402M) COG 2.6pF  $\pm 0.1$ pF 50V  
01005(0402M) COG 2.7pF  $\pm 0.1$ pF 50V  
01005(0402M) COG 2.8pF  $\pm 0.1$ pF 50V  
01005(0402M) COG 2.9pF  $\pm 0.1$ pF 50V  
01005(0402M) COG 3.0pF  $\pm 0.1$ pF 50V  
01005(0402M) COG 3.1pF  $\pm 0.1$ pF 50V  
01005(0402M) COG 3.2pF  $\pm 0.1$ pF 50V  
01005(0402M) COG 3.3pF  $\pm 0.1$ pF 50V  
01005(0402M) COG 3.4pF  $\pm 0.1$ pF 50V  
01005(0402M) COG 3.5pF  $\pm 0.1$ pF 50V  
01005(0402M) COG 3.6pF  $\pm 0.1$ pF 50V  
01005(0402M) COG 3.7pF  $\pm 0.1$ pF 50V  
01005(0402M) COG 3.8pF  $\pm 0.1$ pF 50V  
01005(0402M) COG 3.9pF  $\pm 0.1$ pF 50V  
01005(0402M) COG 4.0pF  $\pm 0.1$ pF 50V  
01005(0402M) COG 4.1pF  $\pm 0.1$ pF 50V  
01005(0402M) COG 4.2pF  $\pm 0.1$ pF 50V  
01005(0402M) COG 4.3pF  $\pm 0.1$ pF 50V  
01005(0402M) COG 4.4pF  $\pm 0.1$ pF 50V  
01005(0402M) COG 4.5pF  $\pm 0.1$ pF 50V

GRM0225C1H4R6BA03L  
GRM0225C1H4R7BA03L  
GRM0225C1H4R8BA03L  
GRM0225C1H4R9BA03L  
GRM0225C1H5R0BA03L  
GRM0225C1H5R1BA03L  
GRM0225C1H5R6BA03L  
GRM0225C1H6R2BA03L  
GRM0225C1H6R8BA03L  
GRM0225C1H7R5BA03L  
GRM0225C1H8R2BA03L  
GRM0225C1H9R1BA03L  
GRM0225C1H100GA03L  
GRM0225C1H120GA03L  
GRM0225C1H150GA03L  
GRM0225C1H180GA02L  
GRM0225C1H220GA02L  
GRM0225C1H270GA02L  
GRM0225C1H330GA02L  
GRM0225C1H390GA02L  
GRM0225C1H470GA02L  
GRM0225C1H560GA02L  
GRM0225C1H680GA02L  
GRM0225C1H820GA02L  
GRM0225C1H101GA02L  
GRM0225C1E221GA02L

01005(0402M) COG 4.6pF  $\pm 0.1$ pF 50V  
01005(0402M) COG 4.7pF  $\pm 0.1$ pF 50V  
01005(0402M) COG 4.8pF  $\pm 0.1$ pF 50V  
01005(0402M) COG 4.9pF  $\pm 0.1$ pF 50V  
01005(0402M) COG 5.0pF  $\pm 0.1$ pF 50V  
01005(0402M) COG 5.1pF  $\pm 0.1$ pF 50V  
01005(0402M) COG 5.6pF  $\pm 0.1$ pF 50V  
01005(0402M) COG 6.2pF  $\pm 0.1$ pF 50V  
01005(0402M) COG 6.8pF  $\pm 0.1$ pF 50V  
01005(0402M) COG 7.5pF  $\pm 0.1$ pF 50V  
01005(0402M) COG 8.2pF  $\pm 0.1$ pF 50V  
01005(0402M) COG 9.1pF  $\pm 0.1$ pF 50V  
01005(0402M) COG 10pF  $\pm 2\%$  50V  
01005(0402M) COG 12pF  $\pm 2\%$  50V  
01005(0402M) COG 15pF  $\pm 2\%$  50V  
01005(0402M) COG 18pF  $\pm 2\%$  50V  
01005(0402M) COG 22pF  $\pm 2\%$  50V  
01005(0402M) COG 27pF  $\pm 2\%$  50V  
01005(0402M) COG 33pF  $\pm 2\%$  50V  
01005(0402M) COG 39pF  $\pm 2\%$  50V  
01005(0402M) COG 47pF  $\pm 2\%$  50V  
01005(0402M) COG 56pF  $\pm 2\%$  50V  
01005(0402M) COG 68pF  $\pm 2\%$  50V  
01005(0402M) COG 82pF  $\pm 2\%$  50V  
01005(0402M) COG 100pF  $\pm 2\%$  50V  
01005(0402M) COG 220pF  $\pm 2\%$  25V

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Murata:

[GRM02-KIT-TTOL-DE](#)