

MWOCP74-3000-A-RM

In Production

Recommended

RoHS

Appearance & Shape



Features

74mm 1U 3000W Front End Power Module

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

MWOC74-3000-A-RM



Specifications

Output power(W)Max	3000W
Total output power(W)	3000W
Form	1U x 73.5 x 550
Vin(VAC)	90Vac to 300Vac
Vin(VDC)	192Vdc to 400Vdc
Vout(V)	12.3V
Vout(V)typ	12.3V
Iout(A)Max	244A
Efficiency(%)	96%
Size(mm)W	73.5mm
Size(mm)L	550.0mm
Size(mm)T	40.0mm
Operating temperature(degC)	0°C to 50°C
Outputs(#)	2
Product series	MWOC74
Product Series Features	74mm Front End DC-DC Power Supply
Safety Approval	UL60950
Vout2(V)	12.2V
Vout2(V)typ	12.2V
Iout2(A)Max	2.5A
Brand	MPS

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, its specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Murata:](#)

[MWOCP74-3000-A-RM](#)