






Chip Antennas

Chip Antennas





● LDA Series



• Terminal of "NC" should be connected to the floating land.
• All the technical data and information contained herein are subject to change without prior notice.


| Part Number | Fo (MHz) | Bandwidth | VSWR (max.) |
|------------------|-------------|-----------|----------------|
| LDA312G4413H-280 | 2442 | - | - |
| LDA312G7313F-237 | 2730 | - | - |
| LDA313G0313F-240 | 3030 | - | - |
| LDA313G3313F-243 | 3330 | - | - |
| LDA315G2013F-246 | 5200 | - | - |
| LDA316G2013F-250 | 6200 | - | - |
| LDA212G3110K-282 | 2310 | - | - |
| LDA212G4410K-283 | 2460 | - | - |
| LDA212G6310K-284 | 2620 | - | - |
| LDA212G6910F-293 | 2690 | - | - |
| LDA212G8610K-285 | 2860 | - | - |
| LDA212G9310F-294 | 2930 | - | - |
| LDA213G1510F-295 | 3150 | - | - |
| LDA213G1610K-286 | 3160 | - | - |
| LDA2H2G6540G-254 | 2650 | - | - |

● ANC Series




Continued on the following page.

Continued from the preceding page.



ANCL11G57SAA165

ANCL11G57SAA166



(in mm)

(in mm)

| Part Number | Fo (MHz) | Bandwidth (MHz) | VSWR (max.) |
|-----------------|----------|-----------------|-------------|
| ANCG11G57SAA136 | 1575 | 2 | 3.0 |
| ANCG11G57SAA137 | 1575 | 2 | 3.0 |
| ANCG11G57SAA146 | 1575 | 2 | 3.5 |
| ANCG11G57SAA160 | 1575 | 2 | 3.5 |
| ANCG12G44SAA145 | 2442 | 84 | 4.0 |
| ANCG12G44SAA148 | 2442 | 84 | 4.0 |
| ANCL11G57SAA165 | 1575 | 2 | 3.0 |
| ANCL11G57SAA166 | 1575 | 2 | 3.0 |

ANCG series are available on ground plane. Please contact us for detail specifications.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Murata:

[LDA2H2G6540G254](#) [LDA313G3313F243](#) [LDA315G2013F246](#) [LDA316G2013F250](#)