

LFD21433MMF5E258

In Production

Recommended

RoHS

REACH

Packaging Information

Packaging	Specifications	Standard Packing Quantity
-	180mm Embossed Tape	4000

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

LFD21433MMF5E258



Specifications

Applications	Zigbee
Nominal Center Frequency (fo)	434.00MHz
Bandwidth(BW)	fo±3.00MHz
Attenuation(Absolute Value) I)	20dB min. at 2f0
Attenuation(Absolute Value) II)	50dB min. at 3f0
Power Capacity	500mW
Operating Temperature Range	-40°C to 85°C
L x W (size)	2.00x1.25mm
Thickness(max.)	0.7mm

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Murata:

[LFD21433MMF5E258](#)