


Product Search Data Sheet

XRCMD32M000FXP50R0



Appearance & Shape





0.45±0.08

Crystal Terminal
No Connect
Crystal Terminal
GND

(in mm)

Note: This datasheet may be out of date. Please download the latest datasheet of XRCMD32M000FXP50R0 from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-us/products/productdetail?partno=XRCMD32M000FXP50R0

Features

The crystal unit that realized small package and highly accurate frequency.

Based on Murata's excellent package technology and high grade quartz crystal elements, achieving small size and high accuracy resonators.

Features

1. The series is available in the applications to be necessary for high accuracy resonator.

2. The resonator is extremerly small size (1612), and contribute to reduction in mounting area.

3. The series complies to RoHS directive, being lead-free (phase 3).

Applications

Other Usage

Consumer



Packaging Information

Packaging	Specifications	Standard
		Packing
		Quantity
R0	180mm Plastic Tape	3000

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering





XRCMD32M000FXP50R0

Note: This datasheet may be out of date. Please download the latest datasheet of XRCMD32M000FXP50R0 from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-us/products/productdetail?partno=XRCMD32M000FXP50R0

Specifications

Product Type	Crystal Unit	
Series	XRCMD	
Туре	MCR1612	
Frequency	32.0000MHz	
Frequency Tolerance	+/-30ppm max. (Total)	
Operating Temperature Range	-30°C~85°C	
Equivalent Series Resistance (ESR)	100ohm max.	
Drive Level (DL)	30µW (100µW max.)	
Load Capacitance (Cs)	6pF	
Shape	SMD	
Wash	Not available (Please be sure to consult with our sales representative or engineer whenever and prior to using the products.)	
L x W (size)	1.6x1.2mm	
Mass	2.9mg	

2 of 2

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Murata: XRCMD32M000FXP50R0