



NA2M-D0B-TX

Miniature transformer balancing adapter, 3 pole XLR male - RCA / phono socket, black coded

Features & Benefits

- The D shape adapters are problem solvers for various intermating problems for professional and semi-professional applications
- Rugged aluminium extrusion housing for best reliability
- colour coding on all RCA types

Miniatur transformer balancing adapters

Low cost solution for unbalanced/balanced line conversion and passive DI applications, where no earth or gain switching is required

Audio transformer 1:1

Impedance ratio: 200:200

Source/load impedance in Ohm: 200/2k, (600/10k)

Max. Input level (@ 50 Hz, 1% THD): -3 dBu

Technical Information

Product	
Title	NA2M-D0B-TX
Connection Type	Adapter

Mechanical	
Wiresize	
Locking device	Latch lock

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Neutrik:](#)

[NA2M-D0B-TX](#)