



## NC3FXX-HD-B-D

Heavy duty female 3 pole XLR cable connector, black housing, for outdoor use.

### Features & Benefits

- Dust and water ingress sealing:
  - IP67 in combination with HD cable connector NC3MXX-HD\*
  - IP67 in combination with HD chassis connector NC3MPR-HD
- Rubber sealing jacket protects against water ingress and mechanical shock
- Gold contacts

## Technical Information

Product	
Title	NC3FXX-HD-B-D
Connection Type	XLR
Gender	female

Electrical	
Capacitance between contacts	$\leq 4 \text{ pF}$
Contact resistance	$\leq 3 \text{ m}\Omega$
Dielectric strength	1,5 kVdc
Insulation resistance	$> 10 \text{ G}\Omega$ (initial), $> 1 \text{ G}\Omega$ (after damp heat test)
Rated current per contact	16 A
Rated voltage	$< 50 \text{ V}$

Mechanical	
Cable O.D.	6.0 - 8.0 mm
Insertion force	$\leq 20 \text{ N}$
Withdrawal force	$\leq 20 \text{ N}$
Lifetime	$> 1000$ mating cycles
Wiresize	max. $2.5 \text{ mm}^2$
Wiresize	max. 14 AWG
Wiring	Solder contacts
Locking device	Latch lock

Material	
Boot	Polyurethan
Contact plating	0.2 µm Au hard alloy over 2 µm Ni
Contacts	Bronze (CuSn8)
Insert	Polyamide (PA66)
Locking element	Zinc diecast (ZnAl4Cu1) / Ck 67 (spring)
Shell	Zinc diecast (ZnAl4Cu1)
Shell coating	Black KTL
Strain relief	Polyacetal (POM)
Sealing jacket	EPDM

Environmental	
Flammability	UL 94 V-0
Standard compliance	IEC 61076-2-103
Solderability	Complies with IEC 68-2-20
Temperature range	-30 °C to +80 °C

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Neutrik:](#)

[NC3FXX-HD-B-D](#)