

NC3MX-1-BAG-D

X-1 series - 3 pin male - black chrome housing/silver contacts. Bulk packed - must order in multiples of 100.

Technical Information

Product	
Title	NC3MX-1-BAG-D
Connection Type	XLR
Gender	male

Electrical	
Capacitance between contacts	$\leq 4\text{ pF}$
Contact resistance	$\leq 3\text{ m}\Omega$
Dielectric strength	1,5 kVdc
Insulation resistance	$> 10\text{ G}\Omega$ (initial)
Rated current per contact	16 A
Rated voltage	$< 50\text{ V}$

Mechanical	
Cable O.D.	3.5 - 8.0 mm
Insertion force	$\leq 20\text{ N}$
Withdrawal force	$\leq 20\text{ N}$
Lifetime	> 1000 mating cycles
Wiresize	max. 2.5 mm^2
Wiresize	max. 14 AWG
Wiring	Solder contacts
Locking device	Latch lock

Material	
Boot	Polyurethan
Contact plating	2 µm Ag
Contacts	Brass (CuZn39Pb3)
Insert	Polyamide (PA66)
Locking element	Zinc diecast (ZnAl4Cu1)
Shell	Zinc diecast (ZnAl4Cu1)
Shell coating	Black KTL
Strain relief	Polyacetal (POM)

Environmental	
Approvals	UL
Flammability	UL 94 V-0
Standard compliance	IEC 61076-2-103
Protection class	IP 40
Solderability	Complies with IEC 68-2-20
Temperature range	-30 °C to +80 °C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Neutrik:](#)

[NC3MX-1-BAG-D](#)