



NF2C/2B

Pair of professional `Phono Plug` (‘RCA`- or `CINCH`- type) - marked 2x black.

Including 2 x 2 strain reliefs for cable O.D. 3.0 mm to 7.3 mm. Additional strain relief for cable O.D. up to 8.0 mm available as accessory.



Features & Benefits

- ✓ Makes ground before signal contact and breaks signal before ground
- ✓ No more disturbing noise and broken speaker cones
- ✓ Precisely machined to our demanding quality standards
- ✓ Neutrik unique chuck type strain relief
- ✓ Gold plated contacts
- ✓ Sleek barrel with soft touch surface and coloured shrink sleeve
- ✓ Improved ground solder lug for ease soldering

Technical Information

Product	
Title	NF2C/2B
Connection Type	Profi
Gender	male

Electrical	
Capacitance between contacts	$\leq 7 \text{ pF}$
Contact resistance	$> 10 \text{ G m}\Omega$
Dielectric strength	1.5 kVdc
Insulation resistance	$> 5 \text{ G}\Omega$
Rated current per contact	depends on mating connector / A
Rated voltage	< 50 V

Mechanical	
Cable O.D.	3.0 - 7.3 mm
Lifetime	> 2000 mating cycles
Wiresize (mm²)	1,5 mm ²
Wiresize (AWG)	16 AWG
Wiring	Solder contacts

Material	
Contact plating	5 µm Au over 5 µm Ni
Contacts	Brass (CuZn39Pb3)
Insert	PBTP 20 % GR
Shell	Brass (CuZn39Pb3)
Strain relief	Polyacetal (POM)

Environmental	
Flammability	UL 94 HB
Standard compliance	IEC 601-14
Protection class	IP 40
Solderability	Complies with IEC 68-2-20
Temperature range	-30 °C to +80 °C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Neutrik](#):

[NF2C/2B](#)