



NKTT*

Patch cable with NP3TT-1 plugs

Part #	Length	Color	Contact plating
NKTT-03BL	30 cm	black	Nickel
NKTT-03BU	30 cm	blue	Nickel
NKTT-03GN	30 cm	green	Nickel
NKTT-03RD	30 cm	red	Nickel
NKTT-03YE	30 cm	yellow	Nickel
NKTT03-B-AU	30 cm	black	Gold
NKTT03-BU-AU	30 cm	blue	Gold
NKTT03-GN-AU	30 cm	green	Gold
NKTT03-R-AU	30 cm	red	Gold
NKTT03-YE-AU	30 cm	yellow	Gold
NKTT-04BL	40 cm	black	Nickel
NKTT-04BU	40 cm	blue	Nickel
NKTT-04GN	40 cm	green	Nickel
NKTT-04RD	40 cm	red	Nickel

NKTT-04YE	40 cm	yellow	Nickel
NKTT04-B-AU	40 cm	black	Gold
NKTT04-BU-AU	40 cm	blue	Gold
NKTT04-R-AU	40 cm	red	Gold
NKTT06-B-AU	60 cm	black	Gold
NKTT06-BU-AU	60 cm	blue	Gold
NKTT-05BL	60 cm	black	Nickel
NKTT-05BU	60 cm	blue	Nickel
NKTT-05GN	60 cm	green	Nickel
NKTT-05RD	60 cm	red	Nickel
NKTT-05YE	60 cm	yellow	Nickel
NKTT06-GN-AU	60 cm	green	Gold
NKTT06-R-AU	60 cm	red	Gold
NKTT06-YE-AU	60 cm	yellow	Gold
NKTT09-B-AU	90 cm	black	Gold
NKTT09-BU-AU	90 cm	blue	Gold
NKTT-1BL	90 cm	black	Nickel
NKTT-1BU	90 cm	blue	Nickel

NKTT-1GN	90 cm	green	Nickel
NKTT-1RD	90 cm	red	Nickel
NKTT-1YE	90 cm	yellow	Nickel
NKTT09-GN-AU	90 cm	green	Gold
NKTT09-R-AU	90 cm	red	Gold
NKTT09-YE-AU	90 cm	yellow	Gold
NKTT-12BL	120 cm	black	Nickel
NKTT-12BU	120 cm	blue	Nickel
NKTT-12GN	120 cm	green	Nickel
NKTT-12RD	120 cm	red	Nickel
NKTT-12RD	120 cm	yellow	Nickel
NKTT12-B-AU	120 cm	black	Gold

Technical Information

Product	
Title	NKTT*
Connection Type	Plug
Gender	male

Mechanical	
Wiresize	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Neutrik:](#)

[NKTT-04BL](#) [NKTT-05RD](#) [NKTT-04RD](#) [NKTT03-B-AU](#) [NKTT-03BL](#) [NKTT-03BU](#) [NKTT-03GN](#) [NKTT03-R-AU](#)
[NKTT-03RD](#) [NKTT-03YE](#) [NKTT04-B-AU](#) [NKTT-04BU](#) [NKTT-04GN](#) [NKTT04-R-AU](#) [NKTT-04YE](#) [NKTT-05BU](#) [NKTT-](#)
[05GN](#) [NKTT-05YE](#) [NKTT-12BL](#) [NKTT-12BU](#) [NKTT-12GN](#) [NKTT-12RD](#) [NKTT-12YE](#) [NKTT-1BL](#) [NKTT-1BU](#) [NKTT-](#)
[1GN](#) [NKTT-1RD](#) [NKTT-1YE](#) [NKTT06-GN-AU](#) [NKTT06-YE-AU](#)