

NMC-C-HR

Lockable USB Type-C chassis with integral USB IF approved receptacle



Features & Benefits

- Push Pull mating design provides secure locking system if mated with NMK-20U*
- Front and rear side mountable
- USB receptacle in scope of delivery
- Reversible USB-C housing
- Guiding housing for better protection of receptacles

Technical Information

Product	
Title	NMC-C-HR

Electrical	
Rated current per contact	5 A
Rated voltage	20 V
Transmission Performance	null

Mechanical	
Body Height	3.16 mm
Body Length	11.3 mm
Body Weight	9.7 g
Orientation	Right Angle
PCB Mounting	HYBRID SMT+DIP
PCB surface center	1.58 mm
Version	USB3.1 Gen.II
Lifetime	10'000 mating cycles
Locking force	50 N
Locking device	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Neutrik:](#)

[NMC-C-HR](#)