

## NYS325

5 pole DIN chassis connector, silver plated contacts



### Article Variations

Article Name	Details	Packaging
NYS325		

## Technical Information

### Product

Title	NYS325
-------	--------

### Electrical

Contact Resistance	<10 mΩ
Insulation Resistance	>1000 MΩ(Initial)
Dielectric Strength	500V dc
Rated Voltage	50 VAC

### Mechanical

Insertion Force	≤40N
Withdrawal Force	>5.5N
Lifetime	>1000 Mating Cycles

### Material

Housing	Aluminum
Shield	Bronze
Rivet	Brass
5 Pin Insulator	PA6+30%GF
Jack	Bronze
Housing	Nickel Plating
Shield	Silver Plating
Jack	Silver Plating

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Neutrik:

NYS325