



RC5F
le rate XLN c con or
REAN®



Article Variations



REAN[®]

		Packaging
	Black plated housing, Silver plated contacts	Plastic bag
	Black plated housing, Silver plated contacts	BULK
RC5F-B	Black plated housing, gold plated contacts	Plastic bag
RC5F-B-D	Black plated housing, gold plated contacts	BULK
RC5F-BAG	Black plated housing, Silver plated contacts	Plastic bag
RC5F-BAG-D	Black plated housing, Silver plated contacts	BULK

Technical Information

Product	
Title	RC5F
Connection Type	XLR
Gender	female

Electrical	
Contact Resistance	≤ 5 mΩ
Insulation Resistance	> 1.5 GΩ



REAN®

Max. Force	≤ 20 N
Cable G	4 - 7 mm
Wiresize	1.5 mm ²
Wiresize	16 AWG

Material	
Plastic Body	PA6+30%GF
Jack	Brass
Ground Contact	Steel
Rubber Ring	Rubber
Button	Zinc
Housing	Zinc
Chuck	POM
Bushing	PA6+30%GF
Push Ring	POM
Boot	PVC
Jack	Sliver Plating
Ground Contact	Tin and Cer
Button	Nickel Plating
Housing	Nickel Plating

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Neutrik:](#)

[RC5F](#) [RC5F-B](#) [RC5F-BAG](#) [RC5F-BAG-D](#) [RC5F-B-D](#) [RC5F-D](#)