



RC5FDL
le plate XLR r contacts sh r L
REAN®



Article Variations

Article Name	Details	Packaging
RC5FDL	Nickel plated housing, tin plated contacts	
RC5FDL-B	Black plated housing, gold plated contacts	

Technical Information

Product	
Title	RC5FDL
Connection Type	XLR
Gender	female



REAN®

R ≤10 A

Mechanical

Lifetime	>1000 Mating Cycles
Insertion Force	≤20N
Withdrawal Force	≤20N

Material

Ground Contact	Bronze
Jack	Brass
Housing	Zinc
Latch	Steel
Spring	Steel
Plastic Body	PA6+30%GF
Ground Contact	Tin and Cer
Jack	Tin and Cer
Housing	Nickel Plating
Latch	Nickel Plating

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Neutrik:](#)

[RC5FDL](#) [RC5FDL-B](#)