



RCX3M-Z-012 **REAN**®



Features & Benefits

- ✓ XLR male cable connector with black plated housing and gold plated contacts
- ✓ Waterproof rating IP65
- ✓ The metal housing is designed with internal threads, to ensure it can withstand gravity under any conditions
- ✓ Cable O.D. : 5-7mm



✓ Therefore, the cable is bent at any Angle, water will not enter the

REAN®

Articles		Packaging
RCX3M-Z-012	Black plated housing, gold plated contacts	BULK
RCX3M-Z-012-1	Black plated housing, gold plated contacts	Plastic Bag

Technical Information

Product	
Title	RCX3M-Z-012
Connection type	XLR
Gender	Male

Electrical	
Contact resistance	< 5 mΩ
Dielectric strength	1.5 kVdc
Dielectric strength	> 10GΩ (Initial)
Rated current per contact	16 A
Rated voltage	< 50 V



REAN®

L ≤ 6 > 1000 mating cycles

Cable G 5.0 - 7.0 mm

Material

Contact	Brass
Contact plating	Gold
Contact ground	Bronze
Contact ground plating	Tin
Shell	Zinc Alloy
shell plating	Black
Chuck	PA
Boot	PA+TPU

Environmental

Solderability	Complies with IEC 68-2-20
Standard compliance	IEC 61076-2-103
Protection class	IP65
Temperature range	-30 °C to +80 °C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Neutrik:](#)

[RCX3M-Z-012-0](#) [RCX3M-Z-012-1](#)