



RLS4FC

4 pole loudspeaker cable connector with latch lock, chuck and bushing, bulk packed, to be ordered in multiples of 100 pcs.

Article Variations

| Article Name | Details | Packaging |
|--------------|------------------------------------|-----------|
| RLS4FC | 4 pole loudspeaker cable connector | BULK |
| RLS4FC-D | 4 pole loudspeaker cable connector | BULK |

Technical Information

Product

| | |
|------------------------|------------------------|
| Title | RLS4FC |
| Connection Type | Loudspeaker Connectors |

Electrical

| | |
|----------------------------------|---|
| Contact resistance | $\leq 5 \text{ m}\Omega$ (after lifetime) |
| Dielectric strength | 4 kVdc (peak) |
| Insulation resistance | $> 1 \text{ G}\Omega$ (after dampheat test) |
| Rated current per contact | 30 A |
| Rated voltage | 250 V (insulation) |
| Attention | Shall NOT be used as an AC mains connector! |

Mechanical

| | |
|-------------------|------------------------|
| Cable O.D. | 6 - 10 mm |
| Lifetime | > 1000 mating cycles |
| Wiresize | 4 mm ² |
| Wiresize | 12 AWG |

Environmental

| | |
|--------------------------|------------------|
| Temperature range | -30 °C to +80 °C |
|--------------------------|------------------|

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Neutrik:](#)

[RLS4FC](#) [RLS4FC-D](#)