

# RP3RC

Stereo 1/4" right-angle plug



## Article Variations

Article Name	Details	Packaging
RP3RC	Nickel plated housing, nickel plated contacts	Plastic Packaging
RP3RC-D	Nickel plated housing, nickel plated contacts	BULK
RP3RC-B	Black plated housing, gold plated contacts	Plastic Packaging
RP3RC-B-D	Black plated housing, gold plated contacts	BULK
RP3RC-BAG	Black plated housing, nickel plated contacts	Plastic Packaging
RP3RC-BAG-D	Black plated housing, nickel plated contacts	BULK

## Product

<b>Title</b>	RP3RC
<b>Connection Type</b>	Plug

## Electrical

<b>Contact rated current</b>	depends on mating connector mΩ
<b>Contact resistance</b>	depends on mating connector mΩ
<b>Dielectric strength</b>	1 kV dc
<b>Insulation resistance</b>	> 1.5 GΩ

## Mechanical

<b>Lifetime</b>	> 1000 mating cycles
<b>Cable O.D.</b>	4 - 7 mm
<b>Wiresize</b>	1.0 mm <sup>2</sup>
<b>Wiresize</b>	18 AWG
<b>Wiring</b>	Solder contacts

## Material

<b>Boot</b>	PA6+30% GF
<b>Contact</b>	Brass ( CuZn39Pb3)
<b>Contact plating</b>	Nickel / Au
<b>Shell</b>	Zinc alloy
<b>Shell plating</b>	Nickel / Black
<b>Strain relief</b>	POM

## Environmental

<b>Temperature range</b>	-20 °C to +70 °C
<b>Flammability</b>	UL 94 HB
<b>Solderability</b>	complies with IEC68-2-20

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Neutrik:](#)

[RP3RC](#) [RP3RC-B](#) [RP3RC-BAG](#) [RP3RC-BAG-D](#) [RP3RC-B-D](#) [RP3RC-D](#)