

# RT3MP

3 pole male TINY xlr receptacle



## Article Variations

Article Name	Details	Packaging
RT3MP	Nickel plated housing, gold plated contacts, max. panel thickness: 6 mm	Plastic Bag
RT3MP-D	Nickel plated housing, gold plated contacts, max. panel thickness: 6 mm	BULK

## Technical Information

### Product

<b>Title</b>	RT3MP
<b>Connection Type</b>	XLR

### Electrical

<b>Contact Resistance</b>	$\leq 10 \text{ m}\Omega$
<b>Insulation Resistance</b>	$> 1 \text{ G}\Omega$
<b>Dielectric Strength</b>	$> 500 \text{ V rms}$
<b>Rated current per contact</b>	$< 5 \text{ A}$

### Mechanical

<b>Lifetime</b>	$> 1000 \text{ Mating Cycles}$
<b>Wiresize</b>	$0.22 \text{ mm}^2$
<b>Wiresize</b>	24 AWG

<b>Material</b>	
<b>Housing</b>	Zinc
<b>Washer</b>	Steel
<b>Nut</b>	Brass
<b>Plastic Body</b>	PA66+30%GF
<b>Pin</b>	Brass
<b>Housing</b>	Nickel Plating
<b>Washer</b>	Nickel Plating
<b>Nut</b>	Nickel Plating
<b>Pin</b>	Gold Plating

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Neutrik:](#)

[RT3MP](#) [RT3MP-D](#)