



RT3MPR
REAN®

Article Variations

Article Name	Details	Packaging
RT3MPR	Nickel plated housing, gold plated contacts, max. panel thickness: 3 mm	Plastic Bag
RT3MPR-D	Nickel plated housing, gold plated contacts, max. panel thickness: 3 mm	BULK

Technical Information

Product	
Title	RT3MPR
Connection Type	XLR

Electrical	
Contact Resistance	$\leq 10 \text{ m}\Omega$
Insulation Resistance	$> 1 \text{ G}\Omega$
Dielectric Strength	$> 500 \text{ V rms}$
Rated current per contact	$< 5 \text{ A}$



REAN®

24 AWG

Material

Housing	Zinc
Nut	Brass
Washer	Steel
Plastic Body	PA66+30%GF
Pin	Brass
Housing	Nickel Plating
Nut	Nickel Plating
Washer	Nickel Plating
Pin	Gold Plating

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Neutrik:](#)

[RT3MPR](#)