



RT4MC-B
le ac 110V xlr 4 pin connector
REAN®

Article Variations

Article Name	Details	Packaging
RT4MC-B	Black plated housing, gold plated contacts	Plastic Bag
RT4MC-B-D	Black plated housing, gold plated contacts	BULK

Technical Information

Product	
Title	RT4MC-B
Connection Type	XLR

Electrical	
Contact Resistance	<10 mΩ
Insulation Resistance	>1 GΩ
Dielectric strength	>500 V rms
Rated current per contact	< 5 A



REAN®

0.22 mm

>10⁶ Mating Cycles

Wire size

24 AWG

Material	
Housing	Zinc
Tube	Aluminum
Pin	Brass
Plastic Body	PA6+30%GF
Ground Contact	Bronze
Chuck	POM
Boot	PC/ABS+TPU
Housing	Nickel Plating
Tube	Black Plating
Pin	Gold Plating
Ground Contact	Tin

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Neutrik:](#)

[RT4MC-B](#)