

RTP3C

Stereo 3 pole



Article Variations

Article Name	Details	Packaging
RTP3C	nickel shell, nickel plated contacts	Plastic Packaging
RTP3C-D	nickel shell, nickel plated contacts	BULK
RTP3C-B	black shell, gold plated contacts	Plastic Packaging
RTP3C-B-D	black shell, gold plated contacts	BULK
RTP3C-BAG	black shell, nickel plated contacts	Plastic Packaging
RTP3C-BAG-D	black shell, nickel plated contacts	BULK

Technical Information

Product

Title	RTP3C
Connection Type	Plug

Electrical

Contact Resistance	≤10 mΩ
Insulation Resistance	>200 MΩ(Initial)
Dielectric Strength	500V dc 50HZ

Mechanical

Insertion and Withdrawal Force	≤60 N
Lifetime	>1,000 Mating Cycles
Cable O.D.	2 - 4 mm
Wiresize	0.24 mm ²
Wiresize	24 AWG

Material

Sleeve Assembly	Brass
Sleeve	Brass
Housing	Zinc
Sleeve Assembly	Nickel Plating
Sleeve	Nickel Plating
Housing	Nickel Plating

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Neutrik:](#)

[RTP3C](#) [RTP3C-B](#) [RTP3C-BAG](#) [RTP3C-BAG-D](#) [RTP3C-B-D](#) [RTP3C-D](#)