




SYMBOL	REVISION	DATE

This drawing is for mechanical mounting information only.
Detailed display specifications can be viewed by downloading
the full datasheet for the appropriate 7.0" TFT, accessible by the link below:

<http://www.newhavendisplay.com/specs/NHD-7.0-800480EF-ATXL-CTP.pdf>
<http://www.newhavendisplay.com/specs/NHD-7.0-800480EF-ASXV-CTP.pdf>
<http://www.newhavendisplay.com/specs/NHD-7.0-800480EF-ASXN-CTP.pdf>

STANDARD TOLERANCES (UNLESS OTHERWISE SPECIFIED)		NEWHAVEN DISPLAY INTERNATIONAL	
LINEAR: ± 0.3 mm		DRAWING/PART NUMBER: NHD-7.0-800480MB-xxxx-CTP	REVISION: 1.0
UNLESS OTHERWISE SPECIFIED		DRAWN BY: N. Patel	CHECKED BY: M. LaVine
- DIMENSIONS ARE IN MILLIMETERS		APPROVED BY: M. LaVine	SIZE: A3
- THIRD ANGLE PROJECTION		DRAWN DATE: 12/4/17	CHECKED DATE: 12/7/17
		APPROVED DATE: 12/7/17	SCALE: 1:2
DO NOT SCALE DRAWING			SHEET 1 OF 1
THIS DRAWING IS SOLELY THE PROPERTY OF NEWHAVEN DISPLAY INTERNATIONAL, INC. THE INFORMATION IT CONTAINS IS NOT TO BE DISCLOSED, REPRODUCED OR COPIED IN WHOLE OR PART WITHOUT WRITTEN APPROVAL FROM NE WHAVEN DISPLAY.			

- NOTES (Mounting Bracket):
1. MATERIAL: SGLCC
 2. THICKNESS: 1.2mm
 3. 4x Mounting Holes, compatible with Rack Unit (RU) spacing
 4. 4x Blind Threaded Standoffs (M3) on back side, suitable for Custom PCB assembly

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Newhaven Display:

[NHD-7.0-800480MB-ASXN-CTP](#)