



- NOTES (Mounting Bracket):
1. MATERIAL: SGLCC
 2. THICKNESS: 1.2mm
 3. 4x Mounting Holes, compatible with Rack Unit (RU) spacing
 4. 4x Blind Threaded Standoffs (M3) on back side, suitable for Custom PCB assembly

Detail: A
1:1
Part# BS04-M3-6 or Equivalent

This drawing is for mechanical mounting information only.
Detailed display specifications can be viewed by downloading
the full datasheet for the appropriate 4.3" TFT, accessible by the link below:

<http://www.newhavendisplay.com/specs/NHD-4.3-800480CF-ASXP.pdf>

STANDARD TOLERANCE: (UNLESS OTHERWISE SPECIFIED)			
LINEAR: ±0.3mm		DRAWING/PART NUMBER: NHD-4.3-800480MB-ASXP	
UNLESS OTHERWISE SPECIFIED:		DRAWN BY: P.Keshavarzi	APPROVED BY: P. Bartek
- DIMENSIONS ARE IN MILLIMETERS		DRAWN DATE: 11/21/19	APPROVED DATE: 11/25/19
- THIRD ANGLE PROJECTION 		DO NOT SCALE DRAWING	
THIS DRAWING IS SOLELY THE PROPERTY OF NEWHAVEN DISPLAY INTERNATIONAL, INC. THE INFORMATION IT CONTAINS IS NOT TO BE DISCLOSED, REPRODUCED OR COPIED IN WHOLE OR PART WITHOUT WRITTEN APPROVAL FROM NEWHAVEN DISPLAY.		SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Newhaven Display:

[NHD-4.3-800480MB-ASXP](#)