


PART NUMBERS	OUTSIDE DIAMETER	MAX. CABLE DIAMETER			
	A	B	C	D	E
162-000-925R000	0.400	0.185	0.248	0.290	0.324
162-000-037R000	0.620	0.300	0.400	0.490	X
162-000-050R000	0.720	0.320	0.410	0.490	0.650

MATERIAL SPECIFICATIONS:

GROMMETS: NON-CONDUCTIVE BLACK PVC
 OPERATING TEMPERATURE: -40°C to 120°C



Only (3x) grommets included with part number 162-000-037R000.

Not designed to work with NorComp 981 Series // Please test within your application to ensure form, fit, and function if using with NorComp 981 Series.

RoHS COMPLIANT

UNITS = inch [mm]

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
P. JENKINS

DATE:
03/12/2005

NorComp

SCALE:
NTS

SHEET 1 OF 1

REV 8

DWG NO.

162-000-YYYYR000

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NorComp:](#)

[162-000-925R000](#) [162-000-037R000](#) [162-000-050R000](#)