






GOLD PLATING THICKNESS
IS BETWEEN 1u" AND 1.5u"



MATERIAL: BRASS

WIRE SIZE: 24-28 AWG



NOTE #1: CONTACTS SUPPLIED ON 500 PC BAGS.
NOTE #2: RECOMMENDED MAX. INSULATION DIAMETER.
FOR 24-28 IS 0.035".

WIRE SIZE

PLATING:	24-28
GOLD FLASH ON MATING AREA NICKEL ON WIRE CRIMP	170-102-170L001
.000010" GOLD OVER .000050" NICKEL ENTIRE CONTACT	170-102-170L002
.000030" GOLD OVER .0001000" NICKEL ENTIRE CONTACT	170-102-170L003

RoHS COMPLIANT

UNITS = inch

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE
THE PROPERTY OF NorComp AND SHALL NOT
BE REPRODUCED, COPIED OR USED AS THE
BASIS FOR THE MANUFACTURE OR SALE OF
APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
PAM JENKINS
DATE:
05/28/2002

NorComp

SCALE:
NTS

SHEET OF
1 1

REV
4

DWG NO. 170-102-170L00Y

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NorComp:](#)

[170-102-170L003](#)