




MATERIAL/FINISH:

SHELL: SPCC, NICKEL PLATED
 BRACKET: BRASS, NICKEL PLATED
 INSULATOR: PBT OR PA9T, UL 94V-0, BLACK,
 PROCESS TEMP: 230°C for 3 seconds (PBT), 2 CYCLES
 260°C for 5 seconds (PA9T), 2 CYCLES
 CONTACT: BRASS, TIN PLATED
 GOLD PLATED - MATING AREA
 BRIGHT TIN - TERMINATING AREA
 BOARDLOCK: COPPER ALLOY, TIN PLATED
 RIVET: COPPER ALLOY, NICKEL PLATED

ELECTRICAL:

RATED CURRENT: 3 AMPS
 RATED VOLTAGE: 250 VAC (rms) MAX.
 WITHSTANDING VOLTAGE: 500 VAC (rms) FOR 1 Min.
 INSULATION RESISTANCE: 1,000 MOhms MIN.
 CONTACT RESISTANCE: 25 mOhms Max.
 OPERATING TEMPERATURE: -55° ~ +85° C

TOTAL MATING FORCE: 6.0 Kgf MAX.
 TOTAL UNMATING FORCE: 1.2 Kgf MIN.

200-015-2 1 3LYY Y

SERIES
 No. of POSITIONS
 GENDER
 1 = FEMALE
 TERMINATION
 1 = PC MOUNT
 SHELL PLATING
 3 = NICKEL
 INSULATOR MATERIAL
 L = PBT
 R = PA9T
 HARDWARE OPTIONS
 SEE PAGE 2
 PLATING OPTIONS
 7 = GOLD FLASH (MATING AREA)
 BRIGHT TIN (SOLDER TAILS)
 9 = 30u" GOLD (MATING AREA)
 BRIGHT TIN (SOLDER TAILS)

RoHS COMPLIANT

UNITS = mm

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

M. SIGMON

DATE:

10/26/2016

NorComp

SCALE:

NTS

SHEET

OF

1

2

REV

4


DWG NO.

200-015-213LYYY

HARDWARE OPTIONS


Ø0.120 [Ø3.05]
HOLE IN FLANGE

00 OPTION





4-40 THREADED HOLE

53 OPTION



4-40 SCREWLOCK
(0.228 [5.80] x 0.374 [9.50])

56 OPTION



RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
M. SIGMON

DATE:
10/26/2016

UNITS = mm

DO NOT SCALE FROM DRAWING

NorComp

SCALE:
NTS

SHEET OF
2 2

REV
4

DWG NO. 200-015-213LYYY

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NorComp:](#)

[200-015-213L567](#) [200-015-213L009](#) [200-015-213L007](#)