


DESCRIPTION: M5 MALE - CABLE MOUNT - SOLDER CUP - 2 POSITION - SHIELDED



# NOTE:

## MATERIAL

HOUSING: TPU, BLACK  
CONTACT: BRASS  
NUT: BRASS  
SHELL: BRASS

## FINISH

CONTACT: GOLD PLATED  
OVER 50μ" NICKEL  
NUT: NICKEL PLATED  
SHELL: BRIGHT TIN PLATED

## ELECTRICAL



RATED CURRENT: 1A  
RATED VOLTAGE: 60V  
INSULATION RESISTANCE: 100 MΩhms MIN.  
CONTACT RESISTANCE: 10 mΩhms MAX.  
WATER PROOF: IP67

## ENVIRONMENT

OPERATION TEMPERATURE: -40°C TO +85°C  
WIRE GAUGE: 28 AWG MAX RECOMMENDED

850-002-103RLSY

1 = GOLD FLASH  
4 = 10μ" GOLD



RoHS COMPLIANT

UNITS = inch [mm]

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

M. SIGMON

DATE:

03-03-16

NorComp

SCALE: NTS

SHEET 1 OF 1

REV 6

DWG NO.

850-002-103RLSY

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

NorComp:

[850-002-103RLU1](#) [850-002-103RLU4](#) [850-002-103RLS1](#) [850-002-103RLS4](#)