





DESCRIPTION: M8 MALE - PANEL MOUNT (FRONT) - SOLDER CUP - 6 POS.



PANEL CUTOUT



NUT



NOTE:

MATERIAL

HOUSING:

PBT UL94V-0, BLACK

CONTACT:

BRASS

SHELL:

BRASS

O-RING:

NBR, BLACK

NUT:

BRASS

FINISH

CONTACT:

GOLD PLATED
OVER 50μ" NICKEL
NICKEL PLATED
NICKEL PLATED

SHELL:

NUT:

ELECTRICAL

RATED CURRENT:

1.5A

RATED VOLTAGE:

30V

INSULATION RESISTANCE:

100 MΩhms MIN.

CONTACT RESISTANCE:

10 mΩhms MAX.

WATER PROOF:

IP67

ENVIRONMENT

OPERATION TEMPERATURE:


-40°C TO +85°C

MAX WIRE AWG:

26

855-006-103R00Y

1 = GOLD FLASH
4 = 10μ" GOLD



RoHS COMPLIANT

UNITS = INCHES [MM]

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

M. SIGMON

DATE:

03-04-16

NorComp

SCALE:

NTS

SHEET

1

OF

1

REV

3

DWG NO.

855-006-103R00Y

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

NorComp:

[855-006-103R004](#) [855-006-103R001](#)