

DESCRIPTION: M8 MALE - PANEL MOUNT (REAR) - SOLDER CUP - 4 POS.


SPECIFICATIONS:

MATERIALS:
HOUSING: PBT, UL94 V-0, BLACK
CONTACTS: GOLD PLATED BRASS (SEE P/N KEY BELOW)
NUT & WASHER: NICKEL PLATED BRASS
SHELL: NICKEL PLATED BRASS
ORING: EPDM, BLACK


ELECTRICAL:
RATED CURRENT: 3A
RATED VOLTAGE: 60V
INSULATION RESISTANCE: 100 MOhms MIN.
CONTACT RESISTANCE: 10 mOhms MAX.

ENVIRONMENT:
OPERATING TEMPERATURE: -40°C TO +85°C
WATER PROOF: IP67

MAX WIRE AWG: 24
MAX TORQUE: 1.25 in-lbs



NUT






WASHER

NOTE:
NUT AND WASHER INTENDED TO BE
INSTALLED OUTSIDE PANEL. CAN OMIT
WASHER TO INCREASE PANEL THICKNESS

855-004-103R00Y

1 = GOLD FLASH
4 = 10u" GOLD



PANEL CUTOUT

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE
THE PROPERTY OF NorComp AND SHALL NOT
BE REPRODUCED, COPIED OR USED AS THE
BASIS FOR THE MANUFACTURE OR SALE OF
APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
M. SIGMON

DATE:
03/04/2016

UNITS = inch [mm]

DO NOT SCALE FROM DRAWING

NorComp

SCALE:
NTS

SHEET
1 OF
1

REV
4

DWG NO.

855-004-103R00Y

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NorComp:](#)

[855-004-103R004](#) [855-004-103R001](#)