

DESCRIPTION: M12 MALE // CABLE MOUNT // SOLDER CUP // 3 POS // HIGH VIBRATION

NOTE:

MATERIAL

HOUSING:

PA66 UL94V-0, BLACK

CONTACT:

BRASS

NUT:

BRASS

O-RING:

EPDM, BLACK

FINISH

CONTACT:

10 μ " GOLD PLATED

NUT:

NICKEL

ELECTRICAL

RATED CURRENT:

4A

RATED VOLTAGE:

250V

INSULATOR RESISTANCE:

100 M Ω hms MIN.

CONTACT RESISTANCE:

10 m Ω hms MAX.

WATER PROOF:

IP67



ENVIRONMENT

OPERATION TEMPERATURE:

-40°C TO +85°C

MAX WIRE AWG:

22 AWG



ANTI-VIBRATION DETENT

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

M. SIGMON

DATE:

08/04/2016

UNITS = inch [mm]

DO NOT SCALE FROM DRAWING

NorComp

SCALE:

NTS

SHEET

OF

1

1

REV

3

DWG NO.

858VA03-103RLU4

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NorComp:](#)

[858VA03-103RLU4](#)