

NOTE:

MATERIAL

HOUSING:

PA66 UL94V-0, BLACK

CONTACT:

BRASS

NUT:

BRASS

O-RING:

EPDM, BLACK

FINISH

CONTACT:

10u" GOLD PLATED

NUT:

NICKEL

ELECTRICAL

RATED CURRENT:

4A

RATED VOLTAGE:

250V

INSULATOR RESISTANCE:

100 MOhms MIN.

CONTACT RESISTANCE:

10 mOhms MAX.

WATER PROOF:

IP67



ENVIRONMENT

OPERATION TEMPERATURE:

-40°C TO +85°C

MAX WIRE AWG:

22 AWG



RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

M. SIGMON

DATE:

08/04/2016

UNITS = inch [mm]

DO NOT SCALE FROM DRAWING

NorComp

SCALE:

NTS

SHEET

1

OF

1

REV

3

DWG NO.

858VA03-203RLU4

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NorComp:](#)

[858VA03-203RLU4](#)