


DESCRIPTION: M12 MALE - CABLE MOUNT - 4 POS.



NOTE:

MATERIAL

HOUSING:
CONTACT:
NUT:
O-RING:
SHELL:

PBT UL94V-0, BLACK
BRASS
BRASS
EPDM, BLACK
BRASS

FINISH

CONTACT:

GOLD PLATED
OVER 50µ" NICKEL
NICKEL PLATED
BRIGHT TIN PLATED

ELECTRICAL

RATED CURRENT:
RATED VOLTAGE:
INSULATION RESISTANCE:
CONTACT RESISTANCE:
WATER PROOF:

4A
250V
100 MOhms MIN.
10 mOhms MAX.
IP67

ENVIRONMENT



OPERATION TEMPERATURE:
MAX WIRE AWG:

-40°C TO +85°C
22

858-004-103RSSY

3 = BRASS/TIN (B/T) SHELL & BRASS/NICKEL NUT
S = STAINLESS STEEL (SS) SHELL & NUT
T = B/T SHELL / SS NUT

1 = GOLD FLASH
4 = 10µ" GOLD



RoHS COMPLIANT

UNITS = INCHES [MM]

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

M. SIGMON

DATE:

03-07-16

NorComp

SCALE:

NTS

SHEET

1

OF

1

REV

3

DWG NO.

858-004-103RSSY

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

NorComp:

[858-004-103RSS1](#) [858-004-103RSS4](#)