



Nut

NOTE:
MATERIAL
Housing: PBT UL94V-0, BLACK
Contact: BRASS
Nut: BRASS
O-Ring: EPDM, BLACK
FINISH
Contact: 10u" GOLD PLATED
Under Plate: NICKEL
Nut: NICKEL
ELECTRICAL
Rated Current: 4A
Rated Voltage: 60V
Insulator Resistance: 100 MΩhms MIN.
Contact Resistance: 10 mΩhms MAX.
Water Proof: IP67
ENVIRONMENT
Operating Temp: -40°C TO +85°C

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
A. Joyner
DATE:
10/30/2020

Tolerance
.X ±0.20
.XX ±0.10
.XXX ±0.05

UNITS = mm

NorComp

DO NOT SCALE FROM DRAWING

SCALE: NTS	SHEET 1	OF 1	REV 2
DWG NO. 858-B05-103RLU4			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NorComp:](#)

[858-B05-103RLU4](#)