

NOTE:

MATERIAL

HOUSING:

PBT UL94V-0, BLACK

CONTACT:

BRASS

NUT:

BRASS

O-RING:

EPDM, BLACK

SHELL:

BRASS

FINISH

CONTACT:

GOLD PLATED

OVER 50 μ " NICKEL

NICKEL PLATED

BRIGHT TIN PLATED

NUT:

SHELL:

ELECTRICAL

RATED CURRENT:

4A

RATED VOLTAGE:

250V

INSULATION RESISTANCE:

100 M Ω hms MIN.

CONTACT RESISTANCE:

10 m Ω hms MAX.

WATER PROOF:

IP67


ENVIRONMENT

OPERATION TEMPERATURE:

-40°C TO +85°C

MAX WIRE AWG:

22



3 = BRASS/TIN (B/T) SHELL & BRASS/NICKEL NUT
 S = STAINLESS STEEL (SS) SHELL & NUT
 T = B/T SHELL / SS NUT

858-D04-103RSSY

1 = GOLD FLASH
 4 = 10 μ " GOLD

RoHS COMPLIANT

UNITS = INCHES [MM]

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

M. SIGMON

DATE:

03-28-16

NorComp

SCALE:

NTS

SHEET

1

OF

1

REV

3

DWG NO.

858-D04-103RSSY

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

NorComp:

[858-D04-103RSS4](#) [858-D04-103RSS1](#)