

DESCRIPTION: M12 // M // 3P SCODE // SOLDER CUP // CABLE MOUNT // UNSHIELDED



SPECIFICATIONS:

MATERIALS:
HOUSING: PA66, UL94 V-0, BLACK
CONTACTS: 10µ" GOLD PLATED BRASS
NUT: NICKEL PLATED BRASS

ELECTRICAL:
RATED CURRENT: 12A
RATED VOLTAGE: 630V
INSULATION RESISTANCE: 100 MOhms MIN.
CONTACT RESISTANCE: 10 mOhms MAX.

ENVIRONMENT:
OPERATING TEMPERATURE: -40°C TO +105°C
WATER PROOF: IP67

MAX WIRE AWG: 18 AWG



RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
J. KADEL

DATE:
12/11/2023

UNITS = mm

DO NOT SCALE FROM DRAWING

NorComp

SCALE:
NTS

SHEET 1 OF 1

REV 0

DWG NO.

858-SP3-103RLU4

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NorComp:](#)

[858-SP3-103RLU4](#)